


# METKON FORCIMAT TS



<b>MODEL NO</b>	<b>FORCIMAT-TS</b>
<b>Operation</b>	Semi Automatic
<b>Application of Force</b>	Individual
<b>Control Panel</b>	Touch Pad Controls
<b>Program Memory</b>	Last Parameters Retained in Memory
<b>Manual Operation Mode</b>	Yes
<b>Head Motor Power</b>	100 W
<b>Sample Holder Rotation Direction</b>	CW
<b>Sample Holder Speed</b>	25-50 RPM
<b>Individual Force</b>	5-60 N
<b>Central Force</b>	None
<b>Grinding Depth Measurement</b>	None
<b>Grinding Depth Measurement Accuracy</b>	None
<b>Disc Cleaning &amp; Drying Feature</b>	Yes
<b>Smart Water Saving Feature</b>	Yes
<b>Compatible Instruments</b>	FORCIPOL-TS
<b>Compressed Air Requirement</b>	6 Bars
<b>Dimensions, WxDxH, (cm)</b>	26 x 46 x 54 (above FORCIPOL working disc)
<b>Weight, kgs</b>	